






# Print on Cardstock


1:144 STS-110 Payload bay






Robotic Arm  
Support arms



CAMERA



KU-Band  
antenna





Print on Cardstock

Open - Payload bay model version


1:144

OV-104  
OV-105


5th modification  
2nd and 3rd modification

Rev. 1

Right side



Left side





# Print on Paper

## Remote Manipulator Arm

The Remote Manipulator Arm will not be articulated. It's a single piece. You can use a cotton swab because it matches the thickness of the Arm for this scale. (2.0 mm)  
Remove the cotton and cover the swab with this paper part. You will need another swab to complete the length of the Remote Manipulator Arm. You can be creative by using any other material for the Arm.

